

**CHOOSE YOUR  
CORIOLIS FLOW METER**

**0.1%**  
Liquid Mass  
Flow

**Smart Meter  
Verification™**

**2/4**  
Wire Cabling

**Data Historian**

**Bluetooth/  
WIFI Config**

**Drainable  
3A & EHEDG**

**SIL ✓**  
Functional  
Safety



**G-Series**



**F/H-Series**



**ELITE**

<b>Line Size</b>	5 line sizes ¼" - 3" DN6 to DN80	7 sizes ¼" - 3"	14 sizes 1/10" - 14"
<b>Turndown</b>	Moderate 8:1	Competitive 20:1	Market Leading > 30:1
<b>Liquid Flow</b>	±0,1%	±0,05%	±0,05%
<b>Gas Flow</b>	±0,5%	±0,35%	±0,25%
<b>Density</b>	±5 kg/m3	±0.5 - 2 kg/m3	±0.2 - 0,5 kg/m3
<b>High Temp</b>	150°C	204°C - 350°C	350°C - 427°C
<b>2 Phase Flow</b>	—	◐ Suitable Low Hz	● Preferred Ultra Low Hz
<b>Cryogenic</b>	—	◐ ETO	● -240°C
<b>Corrosive Material</b>	—	● C22	● C22
<b>Custody Transfer</b>	—	◐ OIML MID Liquid	● OIML MID Liquid + Gas
<b>Custom Calibration</b>	—	—	● Available ISO17025
<b>Advanced Measurement Software</b>	—	—	● PWL 0,1% Gas APM

**Market Leading  
Compactness**  
Weight / Flag / F2F



**Market Leading  
Flow Performance**  
Temperature & Pressure  
Effects / Viscosity / Entrained Air /  
Zero Stability