

## Branson™ Boosters and Converters



**Converters and Boosters Now Available for Next Day Delivery\***



### Product Advantages Header

Over time, critical components can wear causing unplanned downtime, so maintaining your ultrasonic welder's optimum performance levels is critical to your manufacturing throughput. To help keep the costs of downtime to a minimum, Emerson has added a selection of the most commonly used Branson converters and boosters to our next day shipping program. Should you require an urgent replacement, call us, order your parts and they will be shipped out and delivered to you the next day.

#### Key industries

- Automotive
- Medical
- Food Processing
- Business & Consumer Electronics
- Textile
- Packaging

\*(Note: images for reference only and may not be included in program offering.)



\* Available within the United States only

**BRANSON™**

  
**EMERSON™**

## Ordering information

- All orders must be placed with the Branson Parts Department.  
The Part Store contact information is (877) 330 0405 ext. 2008 or by e-mail at Branson.Parts@emerson.com
- Order must be placed before 1pm CST
- Available within the United States only
- Quantity of 3 or less
- Customer must have an account with Branson and on good financial standing

### CONVERTERS

Part Number	Description
101-135-067R	CONVERTER MODEL 4TH
101-135-059R	CONVERTER 20khz CJ-20
101-135-042R	CONV 4TR 40KHZ (CONN)
101-135-068R	CONV 4TP 40KHZ PLATEN
101-135-065R	CONVERTER 932R
101-135-060R	CONVERTER 20khz CR-20
125-135-115R	CONVERTER CR-20S
101-135-041R	CONV 4TJ 40KHZ
101-135-032R	CONVERTER 502
101-135-048R	CONVERTER 902R
159-135-091	CONVERTER 20khz SIP SPECIAL
101-135-081R	CONVERTER 30KHZ CR-30
159-135-212R	ASSY CONV CS-30C SOLID MOUNT
159-135-110R	ASSY CONV 30khz Solid Mount
101-135-071R	CONVERTER 30KHZ CH-30
159-135-138R	CONV CS-20 20 KHZ SOLID MOUNT
101-135-015R	CONVERTER TW-1 (75u) LOW GAIN
159-135-069R	CONVERTER 15khz CJ-15
100-246-612	ASSY SLEEVE CONVERTER
159-135-257	CONVERTER CH-20-8 SOLID SHV
159-135-111R	CONV CP30 30khz PLATEN
125-135-130	CONVERTER 4TP R/A RF
1016556	CONVERTE AMC 4080 4M
1016555	CONVERTER AMC 4080 2M
101-135-124	CONV 20KHZ 5.5kw
1017294	CONVERTER AMC 4080

### BOOSTERS

Part Number	Description
101-149-053	BOOSTER SILVER (500)
101-149-051	BOOSTER GREEN (500)
101-149-093	BOOSTER ASSY 489 1:1
101-149-097	BOOSTER 900 SLD MT 1:1.5
101-149-094	BOOSTER ASSY 489 1:2 SILV
101-149-058	BOOSTER SILVER 152/180 TI
101-149-079	BOOSTER 40KHZ GREEN
101-149-080	BOOSTER 40KHZ GOLD
101-149-052	BOOSTER GOLD (500)
101-149-117	BOOSTER GOLD 30K TI W/O
101-149-056	BOOSTER GREEN 152/180 TI
101-149-059	BOOSTER BLACK 152/180 TI
101-149-057	BOOSTER GOLD 152/180 TI
101-149-092	BOOSTER ASSY 489 1:1.5 GO
101-149-098	BOOSTER 900 SLD MT 1:2
101-149-090	BOOSTER ASSY 489 1:.6
101-149-086	BOOSTER GOLD TI
101-149-116	BOOSTER SILVER 30K TI W/O
101-149-096	BOOSTER ASSY 900 SLD MT 1
101-149-084	BOOSTER BLACK TI
101-149-105	BOOSTER GOLD 30KHZ TI
101-149-083	BOOSTER SILVER TI
101-149-106	BOOSTER GREEN 30KHZ TI

For information on about products, aftermarket services and other programs provided by Emerson, please contact your local Emerson Sales representative.

**BRANSON**<sup>™</sup>

The Emerson logo is a trademark and service mark of Emerson Electric Co. Brand logotype are registered trademarks of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2023 Emerson Electric Co. All rights reserved.  
Based on FL000081ENUS-02\_09-23

  
**EMERSON**<sup>™</sup>