

Complete Marine Expertise

We Provide Innovative Solutions to Operate Safely, Efficiently and with Peace of Mind.

1960 Parent company formed

- C. O. Hansen starts production in Naestved, Denmark
- Acquired by Superfoss in 1969

1984 Danfoss into Marine

- Superfoss Hydraulics is acquired by Danfoss forming Danfoss Marine Systems

2000 Expansion into TLG

- SF-Control acquired by Saab Marine Electronics adding the LevelDatic brand to the system portfolio

2001 Emerson acquires Saab Marine Electronics

- Saab Marine Electronics AB is acquired by Emerson forming Saab Rosemount AB

2007 Emerson acquires Damcos and the Marine Group is formed

- Emerson acquires Damcos A/S
- Saab Rosemount AB changes name to Rosemount Tank Radar AB
- Damcos A/S and Rosemount Tank Radar AB integrate into Marine Tank Management

2013 Greece Establishment

- Marine Tank Management establishes regional sales and service facilities in Greece

2016 All Emerson

- Marine Tank Management name change to Emerson (Marine Solutions)

1983 First Mover Technology

- Saab Marine Electronics formed to design, develop and market radarbased cargo tank monitoring systems

1996 VRC Consolidation

- Nordisk Marine Hydraulik acquired by Danfoss Marine Systems

2000 Automation & TLG Expansion

- Korean JV partner Samgong is acquired by Danfoss Marine Systems
- IPH Marine Automation acquired by Danfoss Marine Systems adding the MAS2600 brand to the system portfolio

2005 China Establishment

- Danfoss Marine Systems acquired by Damcos A/S
- Damcos A/S establish own production facility in Shanghai, China

2011 UAE Establishment

- Marine Tank Management establishes regional sales and service facilities in Dubai

2015 Micro Motion Marine into MTM

- Micro Motion marine business integrated into Emerson's Marine Tank Management organization

Complete Expertise within Marine

Emerson's marine solutions are developed for harsh sea environment to ensure reliable, efficient and safe operation on board any type of ship and offshore unit.

- Integrated control and monitoring
- Cargo monitoring and tank gauging
- Valve remote control
- Fuel management

What really sets us apart is our dedication to the marine sector and engineering excellence. This is reflected in all aspects of our organization, from design and production to application

know-how and global service network. What really drives us is to provide innovative solutions for our customers to operate safely, efficiently and with peace of mind.

Contact us

Europe

Denmark: T: +45 55 78 72 00
Sweden: T: +46 31 337 00 00
Greece: T: +30 69 7255 5976

Asia Pacific

China: T: +86 (21) 5858 9666 801
South Korea: T: +82 51 602 5600
Singapore: T: +65 68 63 2222

Middle East / Africa

UAE: T: +97 15 51236 663

North America

Houston, TX: T: +1 2819884000

For contact information, addresses and facts about our global sales and service network, please visit:

www.Emerson.com/marine



Ed 4, Nov 2019

© Emerson Automation Solutions 2019.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount and Rosemount Logotype are trademarks of Rosemount Inc. Damcos trademark and logotype are trademarks of Damcos A/S. LevelDatic is a trademark of Rosemount TankRadar AB. HART is a registered trademark of the FieldComm Group. All rights reserved.

